



Platform and Handrail Assembly

Start by attaching the platform to the platform support using 5/16" x 1" bolts and nuts. Place all the vertical angles in place, making sure to place the vertical entrance angle to the left front corner of the platform. After all vertical angles are in place, attach front and side handrails as shown in *Figure 1*. Use 5/16" x 1" bolts and nuts in all connections.




Figure 1

Ref #	Part #	Description
A	LS-294	24-7/16" Side Handrail Angle
B	LS-295	32-1/16" Front Handrail Angle
C	LS-6776	11-5/16" Safety Cage Hoop Adapter Angle
D	LS-373	Platform

Ref #	Part #	Description
E	LS-371	42" Platform Vertical Angle (Yellow)
F	LS-6621	46" Vertical Entrance Angle (Orange)
G	LS-6775	67-1/2" Safety Cage Platform Extension Angle

Date: 01-30-14



Eave Platform Assembly Instructions

Platform Support Assembly

When starting the platform support, attach the mounting angle to the sidewall of the grain bin. [Refer to Page 1](#) for the correct holes to be used by the platform. Attach the angle using 5/16" x 1" bolts and nuts and tighten at this time. Next, bolt the support angle to the mounting angle using the proper holes. Attach the brace angle to the mounting angle as shown in [Figure 2](#). Use 5/16" x 1" bolts and nuts for all connections.




Figure 2

Ref #	Part #	Description
A	LS-6705	34" Platform Mounting Angle
B	LS-369	30-3/4" Brace Angle
C	LS-370	28" Support Angle
D		Horizontal Seam

Eave Platform Assembly Instructions

Ref #	Part #	Color Code	Length
1	LS-294	White	24-7/16"
2	LS-295	Black	32-1/16"
3	LS-368	Blue	35-9/16"
4	LS-369	Light Blue	30-3/4"
5	LS-370	Red	28"
6	LS-371	Yellow	42"
7	LS-372	Orange	46"
8	LS-4355	Green	33"
9	LS-5286	Fluorescent Green	36-1/2"
10	LS-6621	Pink	46"
11	LS-6623	Blue/Yellow	35-1/2"
12	LS-6624	Purple	51-5/8"
13	LS-6625	Gold	51-5/8"
14	TDP-5000	Brown	59"
15	TDP-5001	Pink/Fluorescent Green	27"
16	TDP-5002	Pink/Brown	30"
17	TDP-5003	Red/Black	36-7/8"
18	TDP-5004	Orange/Blue	26-1/2"
19	TDP-5005	Light Blue/Black	58-1/2"
20	TDP-5007	Orange/Black	50-5/8"
21	TDP-5008	White/Black	58"
22	TDP-5008N	Fluorescent Green/Black	58"
23	TDP-5009	Yellow/Black	43-1/2"
24	TDP-5011	Red/Blue	29-3/4"