

Rack and Pinion Installation

- 1. Make sure all gates are fully closed.
- 2. Slip rack and pinion tube over (C) center gate control rod and align holes. Make sure rack and pinion (B) is fully extended toward bin wall. (See Figure 1.)
- 3. With rack and pinion resting on unload tube and with tube holes aligned, insert one 5/16" x 1-3/4" bolt (D) through the rack and pinion tube (C) and center gate control rod. Fasten together with a nut. (See Figure 1.)
- 4. Slide wrench (G) assembly over shaft on rack and pinion. Make sure the collar faces the gears. Fasten down with 3/8" flat washer (F) and 3/8" x 3/4" hex bolt (E). (See Figure 2 on Page 2.)





Figure 1

Ref #	Description	
Α	Center Well Control Rod	
В	Rack and Pinion	
С	Rack and Pinion Tube	
D	5/16" x 1-3/4" Bolt	

Date: 10-12-15 V2.0




Ref #	Description
В	Rack and Pinion
E	3/8" x 3/4" Hex bolt
F	Flat washer
G	Wrench

Figure 2

5. With rack and pinion fully extended, attach lower half band (H) and secure to unload tube with six (6) 5/16" x 1-1/2" bolts (I), washers and serrated flange nuts, three (3) on each side. (See Figure 3.)

Ref#

6. To open all gates, with center gate closed, place second 5/16" x 1-3/4" bolt through center gate control rod (J) and intermediate gate control rod (K) and secure with nut. (See Figure 3.)




Н	Lower Half Band	
I	5/16" x 1-1/2" Bolts	
J	Center Well Control Rod	
K	Intermediate Well Control Rod	

Description

Figure 3

PNEG-1443 Page 2 of 4

8" and 10" Rack and Pinion Parts



Page 3 of 4 PNEG-1443

8" and 10" Rack and Pinion Parts List

Ref #	Part #	Description
3	GK6838	8" Rack and Pinion Housing Assembly
3	GK6966	10" Rack and Pinion Housing Assembly
4	GK80079	8" Rack and Pinion Body Assembly
4	GK80080	10" Rack and Pinion Body Assembly
5	GC09859	Spur Gear 10DP 1" Face 22T
6	GK6841	Rack and Pinion Spacer Tube
7	GK4211	1" I.D. x 1-1/2" O.D. Flat Washer 10 Gauge Zinc
8	GK6845	Rack and Pinion Crank Shaft
9	S-4377	5/16" x 2" Grooved Roll Pin
10	GK1603	8" Half Band
10	GK5116	10" Half Band
11	S-2741	5/16"-18 x 1-1/2" HHCS Zinc Grade 5
12	S-845	5/16" Flat Washer Zinc Grade 2
13	S-10268	Flange Nut, 5/16"-18 JS500 Grade 5
14	S-7149	5/16"-18 x 1-3/4" HHTB Grade 5
15	S-7484	Hex Nut, 5/16"-18 JS500 Grade 5
16	S-9067	3/8"-16 x 3/4" Flange Bolt Zinc Grade 5
17	S-248	3/8" Flat Washer Zinc Grade 2
18	GK7260	3/4" Wrench Assembly
19	GC10316	Rack Bar 10P x 1" x 14"
20	S-8999	5/16"-18 x 1/2" HHCS Zinc Grade 5

PNEG-1443 Page 4 of 4